

# FLX-D37M/SHORTING PLUG - Plug-in bridge



1029334

<https://www.phoenixcontact.com/us/products/1029334>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Shorting plug for use in the TDC3000 migration boards



## Your advantages

- DSUB control side connection
- Used on J2 header when common negative terminals are desired

## Commercial data

Item number	1029334
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2B8H
GTIN	4055626530901
Weight per piece (including packing)	42 g
Weight per piece (excluding packing)	40 g
Customs tariff number	85366990
Country of origin	US

# FLX-D37M/SHORTING PLUG - Plug-in bridge

1029334

<https://www.phoenixcontact.com/us/products/1029334>

## Technical data

### Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


### Product properties

Product type	Bridge
Insulation characteristics	
Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	30 V AC/DC
Nominal current $I_N$	5 A

### Dimensions

Dimensional drawing	
Width	69.49 mm
Height	24.99 mm
Depth	61.02 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Altitude	< 2000 m
Permissible humidity (operation)	< 90 %


# FLX-D37M/SHORTING PLUG - Plug-in bridge

1029334

<https://www.phoenixcontact.com/us/products/1029334>

## Drawings

Dimensional drawing




# FLX-D37M/SHORTING PLUG - Plug-in bridge



1029334

<https://www.phoenixcontact.com/us/products/1029334>

Circuit diagram



# FLX-D37M/SHORTING PLUG - Plug-in bridge



1029334

<https://www.phoenixcontact.com/us/products/1029334>

## Classifications

### ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

### ETIM

ETIM 10.0	EC002886
-----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# FLX-D37M/SHORTING PLUG - Plug-in bridge



1029334

<https://www.phoenixcontact.com/us/products/1029334>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)