

# FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/us/products/1029279>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Blind plug, color: gray



## Commercial data

Item number	1029279
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6114
GTIN	4055626531359
Weight per piece (including packing)	157.4 g
Weight per piece (excluding packing)	157.4 g
Customs tariff number	85389099
Country of origin	PL

# FBP-3F 4U - Blind plug



1029279

<https://www.phoenixcontact.com/us/products/1029279>

## Technical data

### Product properties

Product type	Blind plug
Product family	FAME 3 RACK

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# FBP-3F 4U - Blind plug



1029279

<https://www.phoenixcontact.com/us/products/1029279>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1029279>



**CSA**

Approval ID: 13631



**cUL Recognized**

Approval ID: FILE E 60425



**UL Recognized**

Approval ID: FILE E 60425

# FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/us/products/1029279>



## Classifications

### ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

### ETIM

ETIM 10.0	EC002555
-----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# FBP-3F 4U - Blind plug



1029279

<https://www.phoenixcontact.com/us/products/1029279>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	567f7905-dab1-4a5a-ba00-b928042245d1

### EF3.1 Climate Change

CO2e kg	1.182 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)