

HSCP-CB 6U-7035 - Fastening clip

1037100

<https://www.phoenixcontact.com/us/products/1037100>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ME-IO Blockbelt, for 6 PCB connectors, Blockbelt, width: 8.1 mm, height: 65.7 mm, depth: 1.25 mm, color: light gray (similar RAL 7035)

Your advantages

- Enables the functional grouping of various connector plugs
- Simplifies service and maintenance work
- Fast mounting and removal of the clamps through a latch system

Commercial data

Item number	1037100
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC15
Product key	ACHECZ
GTIN	4055626570044
Weight per piece (including packing)	0.64 g
Weight per piece (excluding packing)	0.64 g
Customs tariff number	85389099
Country of origin	PL

HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

Technical data

Product properties

Product type	Mounting material
Housing type	ME-IO Blockbelt
Housing series	ME-IO
Product family	ME-IO

Dimensions

Width	8.1 mm
Height	65.7 mm
Depth	1.25 mm

Material specifications

Color	light gray (RAL 7035)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in
---------------	---------

HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.019 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com