CRIMPFOX DUO 10 SET - Tool set

1044971

https://www.phoenixcontact.com/us/products/1044971

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, CRIMPFOX DUO 10, AI SORTI BOX RD, AI TWIN SORTI BOX BU, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools
- Universal tools sets with WIREFOX 10, CRIMPFOX-DUO tools from TOOL fox
- Ideal for TWIN ferrule
- Rugged and heavy-duty tool bags

Commercial data

Item number	1044971
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4055626622859
Weight per piece (including packing)	1,040 g
Weight per piece (excluding packing)	1,056.1 g
Customs tariff number	82060000
Country of origin	SE

Set consists of

CRIMPFOX DUO 10 - Crimping pliers

1031721

https://www.phoenixcontact.com/us/products/1031721



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm^2, max. cross section: 10 mm^2, for TWIN ferrules up to 2 x 4 mm^2, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

WIREFOX 10 - Stripping tool

1212150

https://www.phoenixcontact.com/us/products/1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm^2, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm^2 stranded/1.5 mm^2 solid, replaceable stripping blade

AI SORTI BOX RD - Assortment box

3202960

https://www.phoenixcontact.com/us/products/3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

AI-TWIN SORTI BOX BU - Assortment box

3202986

https://www.phoenixcontact.com/us/products/3202986



Assortment box, supplied with TWIN ferrules in accordance with DIN 46228-4, 50 pcs. each AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

https://www.phoenixcontact.com/us/products/1212423



Tool box, unequipped

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Trapezoidal crimp

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black (RAL 9005)

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1044971

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27113200

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	10.209 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com