

# ZB 5,LGS:GROSSBUCHST. N - Zack marker strip



1050059:N

<https://www.phoenixcontact.com/us/products/1050059:N>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, horizontally labeled with the capital letter: N, white, for terminal block width: 5.2 mm, mounting type: latching

## Commercial data

Item number	1050059:N
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918488062
Weight per piece (including packing)	1.332 g
Weight per piece (excluding packing)	1.066 g
Customs tariff number	49119900
Country of origin	DE

# ZB 5,LGS:GROSSBUCHST. N - Zack marker strip



1050059:N

<https://www.phoenixcontact.com/us/products/1050059:N>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	5.2 mm

### Marking

Printing	N
Slot type	high

### Mounting

Mounting type	latching
---------------	----------

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Dimensions

Width	5 mm
Pitch	5.2 mm

#### Text field

Text field width	5.15 mm
Text field height	10.50 mm

### Standards and regulations

Wipe resistance	DIN 30646
	DIN VDE 0611

# ZB 5,LGS:GROSSBUCHST. N - Zack marker strip



1050059:N

<https://www.phoenixcontact.com/us/products/1050059:N>

## Classifications

### ECLASS

ECLASS-13.0

27281101

### ETIM

ETIM 9.0

EC000761

### UNSPSC

UNSPSC 21.0

39131500

# ZB 5,LGS:GROSSBUCHST. N - Zack marker strip



1050059:N

<https://www.phoenixcontact.com/us/products/1050059:N>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Yes, No exemptions

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)