

HC-M-B24-DOCK-H - Docking frame



1051222

<https://www.phoenixcontact.com/us/products/1051222>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Docking frame for 6 modules, fixed assembly, rack compensation of ± 2.0 mm in the x/y-axis



Product description

Docking frame, fixed assembly. Metal, without PE. Rack compensation of ± 2.0 mm in the x/y axis

Commercial data

Item number	1051222
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACZ
GTIN	4055626673042
Weight per piece (including packing)	100.58 g
Weight per piece (excluding packing)	100.58 g
Customs tariff number	85389099
Country of origin	CN

HC-M-B24-DOCK-H - Docking frame



1051222

<https://www.phoenixcontact.com/us/products/1051222>

Technical data

Product properties

Product type	Docking frame
Series	HC-M-B
	HC-M-02
	HC-M-03
	HC-M-03/04
	HC-M-04
	HC-M-05
	HC-M-06
	HC-M-08
	HC-M-08-GBIT
	HC-M-12
	HC-M-17
	HC-M-20
	HC-M-25
	HC-M-DSUB
	HC-M-EMV
	HC-M-HV
HC-M-HS	
HC-M-00	
Application	Modular docking frame
Type	B24
Number of module slots	6
Frame type	Docking frames

Material specifications

Material	Die-cast zinc
----------	---------------

Mounting

Mounting type	Direct mounting with flange
Assembly note	When using the module carrier frame in metal housings, the connection of the PE conductor must be ensured via the PE connection provided on the module carrier frame or via a special metal PE module


HC-M-B24-DOCK-H - Docking frame

1051222

<https://www.phoenixcontact.com/us/products/1051222>


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing




Mounting cutout

HC-M-B24-DOCK-H - Docking frame

1051222

<https://www.phoenixcontact.com/us/products/1051222>

Dimensional drawing



Schematic drawing of docking frame

HC-M-B24-DOCK-H - Docking frame



1051222

<https://www.phoenixcontact.com/us/products/1051222>

Classifications

ECLASS

ECLASS-13.0	27440206
ECLASS-15.0	27440206

ETIM

ETIM 10.0	EC002312
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-M-B24-DOCK-H - Docking frame



1051222

<https://www.phoenixcontact.com/us/products/1051222>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com