

# TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for printing WMS-OT/WMS-2 HF... and TMT (Ex..)R materials, length: 300 m, roll length: 300 m, width: 25 mm, color: black

## Commercial data

Item number	1053499
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4055626685717
Weight per piece (including packing)	82 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	96121010
Country of origin	DE

# TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	25 mm
Length	300 m
Length of roll	300 m

### Material specifications

Color	black (RAL 9005)
-------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	30 %

# TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

## Classifications

### ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

### ETIM

ETIM 10.0	EC001694
-----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)