

# CEC PTPOWER 35/50 - Cover



1056086

<https://www.phoenixcontact.com/us/products/1056086>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, yellow (RAL 1018), labeled: Lightning flash, mounting type: plug in



## Your advantages

- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented

## Commercial data

Item number	1056086
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4055626694283
Weight per piece (including packing)	3.33 g
Weight per piece (excluding packing)	3.33 g
Customs tariff number	85369010
Country of origin	TR

1056086

<https://www.phoenixcontact.com/us/products/1056086>

## Technical data

### Notes

Note on application	Use for unused terminal points
---------------------	--------------------------------

### Product properties

Product type	Warning label printed
Type	Closed housing

### Marking

Printing	Lightning flash
----------	-----------------

### Dimensions

Width	14.80 mm
Height	37.76 mm
Depth	43.30 mm

### Material specifications

Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	plug in
---------------	---------

# CEC PTPOWER 35/50 - Cover



1056086

<https://www.phoenixcontact.com/us/products/1056086>

## Classifications

### ECLASS

ECLASS-13.0	27281107
ECLASS-15.0	27281107

### ETIM

ETIM 10.0	EC001777
-----------	----------

### UNSPSC

UNSPSC 21.0	55121700
-------------	----------

# CEC PTPOWER 35/50 - Cover



1056086

<https://www.phoenixcontact.com/us/products/1056086>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.02 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)