

ZB10,LGS:SYMBOLE L2 - Marker for terminal blocks



1053098:L2

<https://www.phoenixcontact.com/us/products/1053098:L2>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, horizontally labeled with the symbol: L2, white, for terminal block width: 10.2 mm, mounting type: latching

Commercial data

Item number	1053098:L2
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2122
GTIN	4017918550905
Weight per piece (including packing)	2.43 g
Weight per piece (excluding packing)	2.101 g
Country of origin	DE

1053098:L2

<https://www.phoenixcontact.com/us/products/1053098:L2>

Technical data

Product properties

Product type	Terminal marker
Pitch	10.2 mm

Marking

Printing	L2
Slot type	high

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Dimensions

Width	10.15 mm
Height	10.5 mm
Depth	4.20 mm
Pitch	10.2 mm

Text field

Text field width	10.15 mm
Text field height	10.50 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZB10,LGS:SYMBOLE L2 - Marker for terminal blocks



1053098:L2

<https://www.phoenixcontact.com/us/products/1053098:L2>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB10,LGS:SYMBOLE L2 - Marker for terminal blocks



1053098:L2

<https://www.phoenixcontact.com/us/products/1053098:L2>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.005 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com