

NBC-R4AC/2,0-93C/OE - Network cable



1076686

<https://www.phoenixcontact.com/us/products/1076686>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, cable length: 2 m, number of positions: 4, cable outlet: straight, Ethernet

Your advantages

- Perfect for industrial applications
- Compact angle
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)

Commercial data

Item number	1076686
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	ABNABA
GTIN	4055626785233
Weight per piece (including packing)	140 g
Weight per piece (excluding packing)	130.241 g
Country of origin	PL

1076686

<https://www.phoenixcontact.com/us/products/1076686>

Technical data

Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Number of positions	4
Cable outlet	straight

Interfaces

Signal type/category	Ethernet
----------------------	----------

Electrical properties

Transmission characteristics (category)	CAT5
---	------

Mechanical properties

Mechanical data

Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

Connector

Connection 1

Type	Plug straight RJ45
Shielded	yes
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Connection 2

Type	free cable end
Degree of protection	IP20

Cable/line

Cable length	2.00 m
Cable type	Ethernet
Signal type/category	Ethernet

NBC-R4AC/2,0-93C/OE - Network cable



1076686

<https://www.phoenixcontact.com/us/products/1076686>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NBC-R4AC/2,0-93C/OE - Network cable



1076686

<https://www.phoenixcontact.com/us/products/1076686>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com