

PATG HF 3/30/BIN - Conductor marker carrier



1069829

<https://www.phoenixcontact.com/us/products/1069829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, Mixed color, unmarked, cable diameter range: 4 ... 7 mm, mounting type: slide-on, text field height: 4 mm, text field width: 30 mm

Commercial data

Item number	1069829
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Product key	BG221A
GTIN	4055626747637
Weight per piece (including packing)	0.856 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

PATG HF 3/30/BIN - Conductor marker carrier



1069829

<https://www.phoenixcontact.com/us/products/1069829>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	30 mm
Height	8.9 mm
Depth	9.1 mm

Text field

Text field width	30 mm
Text field height	4 mm

Material specifications

Color	multicolored (RAL -)
	transparent
	black (RAL 9005)
Material	TPU
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	4 mm ... 7 mm
-------------------------	---------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	slide-on
---------------	----------

PATG HF 3/30/BIN - Conductor marker carrier



1069829

<https://www.phoenixcontact.com/us/products/1069829>

Classifications

ECLASS

ECLASS-13.0

27281105

ETIM

ETIM 9.0

EC002248

UNSPSC

UNSPSC 21.0

39121400

PATG HF 3/30/BIN - Conductor marker carrier



1069829

<https://www.phoenixcontact.com/us/products/1069829>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.129 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com