

FBST 50-PLC BU - Single plug-in bridge



1081051

<https://www.phoenixcontact.com/us/products/1081051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single plug-in bridge, nominal current: 32 A, length: 50 mm, color: blue



Commercial data

Item number	1081051
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	C461
Product key	DK62Z1
GTIN	4055626807072
Weight per piece (including packing)	4.38 g
Weight per piece (excluding packing)	1.6 g
Customs tariff number	85366990
Country of origin	DE

FBST 50-PLC BU - Single plug-in bridge



1081051

<https://www.phoenixcontact.com/us/products/1081051>

Technical data

Product properties

Product type	Bridge
--------------	--------

Electrical properties

Maximum load current	32 A
----------------------	------

Connection data

Maximum load current	32 A
----------------------	------

Dimensions

Length	50 mm
--------	-------

Material specifications

Color	blue (RAL 5015)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (UL (Haz. Loc.))	-40 °C ... 70 °C
--	------------------

Approvals

UL, USA/Canada

Identification	Class I, Zone 2, AEx ec IIC T4
	Class I, Zone 2, Ex ec IIC Gc T4 X

FBST 50-PLC BU - Single plug-in bridge



1081051

<https://www.phoenixcontact.com/us/products/1081051>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1081051>



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E199827

FBST 50-PLC BU - Single plug-in bridge



1081051

<https://www.phoenixcontact.com/us/products/1081051>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBST 50-PLC BU - Single plug-in bridge



1081051

<https://www.phoenixcontact.com/us/products/1081051>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.019 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com