

# EV-T2CCS-MF-M4X45-BIT - Repair kit



1085796

<https://www.phoenixcontact.com/us/products/1085796>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect standard, CCS type 2, Repair kit, Accessories, housing: black, with replaceable mating face frame, with 5x M4X45 rounded head screws with Torx security drive, with special bit (867/4 IPR TORX PLUS® bit, 20 IPR x 89 mm) for insulated screwdriver, for replacement of the mating face frame of vehicle charging connectors, IEC 62196-3, The vehicle connector housing does not have to be opened in order to replace the mating face frame.

## Product description

Repair kit with replaceable mating face frame for CCS type 2 DC vehicle connector

## Commercial data

Item number	1085796
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBMFY
GTIN	4055626874678
Weight per piece (including packing)	218.833 g
Weight per piece (excluding packing)	33 g
Customs tariff number	85389099
Country of origin	PL

# EV-T2CCS-MF-M4X45-BIT - Repair kit



1085796

<https://www.phoenixcontact.com/us/products/1085796>

## Technical data

### Notes

General	The vehicle connector housing does not have to be opened in order to replace the mating face frame.
---------	---

### Product properties

Product type	Repair kit
Product family	CHARX connect standard
Type	Accessories
Design	with replaceable mating face frame with 5x M4X45 rounded head screws with Torx security drive with special bit (867/4 IPR TORX PLUS® bit, 20 IPR x 89 mm) for insulated screwdriver
Charging standard	CCS type 2
Charging mode	Mode 4

### Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

### Standards and regulations

#### Standards

Standards/regulations	IEC 62196-3
-----------------------	-------------

# EV-T2CCS-MF-M4X45-BIT - Repair kit



1085796

<https://www.phoenixcontact.com/us/products/1085796>

## Classifications

### ECLASS

ECLASS-13.0	27144792
ECLASS-15.0	27144792

### ETIM

ETIM 10.0	EC002884
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# EV-T2CCS-MF-M4X45-BIT - Repair kit



1085796

<https://www.phoenixcontact.com/us/products/1085796>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)