

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier



1089388

<https://www.phoenixcontact.com/us/products/1089388>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Socket, M12, A-coding, THR solder connection, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1089388
Packing unit	60 pc
Minimum order quantity	60 pc
Product key	ABQAGG
GTIN	4055626893808
Weight per piece (including packing)	5.541 g
Weight per piece (excluding packing)	2.975 g
Country of origin	DE

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier



1089388

<https://www.phoenixcontact.com/us/products/1089388>

Technical data

Product properties

Product type	Contact insert
Number of positions	8
Shielded	yes
Coding	A
Thread type	M12

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Connector

Connection 1

Head design	Socket
Head thread type	M12
Coding	A

Environmental and real-life conditions

Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier




1089388

<https://www.phoenixcontact.com/us/products/1089388>

Drawings

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier




1089388

<https://www.phoenixcontact.com/us/products/1089388>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1089388>

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier



1089388

<https://www.phoenixcontact.com/us/products/1089388>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FS-8P-L180-THR SHPD - Contact carrier



1089388

<https://www.phoenixcontact.com/us/products/1089388>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com