

# PSR-M-CABLE25 - Cable




1104855

<https://www.phoenixcontact.com/us/products/1104855>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connection cable for TBUS extension in connection with PSR-M-TBUS1 or PSR-M-TBUS2, 25 m



The figure shows a version of the article

## Commercial data

Item number	1104855
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN02
Product key	DNA366
GTIN	4055626973012
Weight per piece (including packing)	2,359 g
Weight per piece (excluding packing)	2,359 g
Customs tariff number	85444995
Country of origin	IT

# PSR-M-CABLE25 - Cable



1104855

<https://www.phoenixcontact.com/us/products/1104855>

## Technical data

### Notes

#### Note on application

Note on application

Only for industrial use

### Product properties

Product type

Adapter cable

### Electrical properties

Impedance

nom. 120  $\Omega$

### Dimensions

#### External dimensions

External diameter max.

9.00 mm

### Material specifications

Outer sheath, material

PVC

### Cable/line

Cable length

25 m

Cable structure

2 x 2 x 24 AWG

External cable diameter

8.70 mm

Outer sheath, material

PVC

External sheath, color

yellow

Shielding

Braided copper wires

Cable resistance

< 95 m $\Omega$ /m

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)

-30 °C ... 60 °C

# PSR-M-CABLE25 - Cable

1104855

<https://www.phoenixcontact.com/us/products/1104855>



## Classifications

### ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

### ETIM

ETIM 10.0	EC002886
-----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# PSR-M-CABLE25 - Cable



1104855

<https://www.phoenixcontact.com/us/products/1104855>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	9.12 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)