

BRIDGE-PT-3-2M/0,3M - Bridge



1107650

<https://www.phoenixcontact.com/us/products/1107650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

3-phase loop bridge for 3 CONTACTRON modules, with Push-in connection and 22.5 mm housing width, cable length between the modules: 0.3 m, connecting cable: 2 m



Your advantages

- Considerable reduction in wiring

Commercial data

Item number	1107650
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C470
Product key	DK74Z1
GTIN	4063151009069
Weight per piece (including packing)	272.15 g
Weight per piece (excluding packing)	254.7 g
Customs tariff number	85444290
Country of origin	DE

BRIDGE-PT-3-2M/0,3M - Bridge



1107650

<https://www.phoenixcontact.com/us/products/1107650>

Technical data

Product properties

Product type	Loop bridge
Product family	CONTACTRON
Number of bridgeable modules	3

Electrical properties

Operating voltage range	42 V AC ... 575 V AC
Operating current	≤ 25 A

Dimensions

Width	22.5 mm
-------	---------

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Cable/line

Connecting cable length	2 m
Cable cross section	2.5 mm ²

BRIDGE-PT-3-2M/0,3M - Bridge





1107650

<https://www.phoenixcontact.com/us/products/1107650>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1107650>

 **UL Listed**
Approval ID: FILE E 172140

 **cUL Listed**
Approval ID: FILE E 172140

 **cUL Listed**
Approval ID: E228652

 **UL Listed**
Approval ID: E228652

BRIDGE-PT-3-2M/0,3M - Bridge



1107650

<https://www.phoenixcontact.com/us/products/1107650>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

BRIDGE-PT-3-2M/0,3M - Bridge



1107650

<https://www.phoenixcontact.com/us/products/1107650>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com