# CUTFOX-MPS - Cutting tool

1139725

https://www.phoenixcontact.com/us/products/1139725

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multifunctional scissors, micro-serrated cutting area, suitable for cardboard, aluminum, Kevlar fibers, and plastic, outside blade edge can be used to safely cut adhesive tape, two-component non-slip soft-grip handles, ergonomic design, adjustable screw joint, with protective cover

## Your advantages

- Microserration for high cutting performance
- Cutting edge made of stainless steel
- Adjustable screw joint
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Plastic holster

## Commercial data

| | |
|---|---|
| Item number | 1139725 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3116 |
| GTIN | 4063151088330 |
| Weight per piece (including packing) | 180 g |
| Weight per piece (excluding packing) | 143.53 g |
| Customs tariff number | 82033000 |
| Country of origin | TW |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Cutting tool |
| Application | Aluminum |
| | Copper |
| | Kevlar fibers |
| | Plastic |
| | Carton |
| Product property | Multipurpose shears |
| | Notched gripping surface |
| | Wire cutting area |
| | Additional blade on blade back |
| | Plastic holster |
| | Microserrated |
| | Ergonomic two-component handle |
| | Adjustable screw joint |

### Connection data

| | |
|---|---|
| Conductor cross-section flexible | 2.5 mm² |

### Dimensions

| | |
|---|---|
| Width | 87 mm |
| Height | 14 mm |
| Length | 208 mm |

### Material specifications

| | |
|---|---|
| Color | multicolored (RAL -) |

### Cable/line

| | |
|---|---|
| External cable diameter | ≤ 2.50 mm |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21044701 |
| ECLASS-15.0 | 21044701 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000142 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 2.479 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com