

# SAC-4P-M12MS/ 1,5-PUR BK - Sensor/actuator cable



1145885

<https://www.phoenixcontact.com/us/products/1145885>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, Plug straight M12, coding: A, on free cable end, cable length: 1.5 m

## Commercial data

Item number	1145885
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CCA
GTIN	4063151135393
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

1145885

<https://www.phoenixcontact.com/us/products/1145885>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	4

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Outer sheath, material	PUR
------------------------	-----

### Electrical properties

Nominal voltage $U_N$	250 V AC
	250 V DC

### Connection data

#### Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

### Connector

#### Connection 1

Type	Plug straight M12
Coding type	A

#### Connection 2

Type	free cable end
------	----------------

### Cable/line

Cable length	1.5 m
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67
	IP68

# SAC-4P-M12MS/ 1,5-PUR BK - Sensor/actuator cable



1145885

<https://www.phoenixcontact.com/us/products/1145885>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-4P-M12MS/ 1,5-PUR BK - Sensor/actuator cable



1145885

<https://www.phoenixcontact.com/us/products/1145885>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)