

ES-BBC-MF5 - Panel-mount frame



1155609

<https://www.phoenixcontact.com/us/products/1155609>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel-mount frame, Range of articles: BBC, design: Panel-mount frame, color: black



The figure shows a 3-position version

Commercial data

Item number	1155609
Packing unit	4 pc
Minimum order quantity	4 pc
Sales key	AB04
Product key	ABLDAC
GTIN	4063151156077
Weight per piece (including packing)	78 g
Weight per piece (excluding packing)	52.266 g
Customs tariff number	85389099
Country of origin	CN

ES-BBC-MF5 - Panel-mount frame



1155609

<https://www.phoenixcontact.com/us/products/1155609>

Technical data

Product properties

Product type	Panel-mount frame
Product family	BBC
Type	Panel-mount frame
Number of slots	1

Dimensions

Width	68 mm
Height	100.5 mm
Length	41 mm

Material specifications

Color	black
Color of the housing part	black
Material Housing	PA-GF
Flammability rating according to UL 94	V0

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	1
-----------------------------	---

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
---------------------------------	------------------

ES-BBC-MF5 - Panel-mount frame



1155609

<https://www.phoenixcontact.com/us/products/1155609>

Classifications

ECLASS

ECLASS-15.0	27440210
ECLASS-13.0	27440192

ETIM

ETIM 10.0	EC002310
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ES-BBC-MF5 - Panel-mount frame



1155609

<https://www.phoenixcontact.com/us/products/1155609>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com