

SCX-CLAMP 14X51-127 - Mast clamp



1175556

<https://www.phoenixcontact.com/us/products/1175556>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mast clamps, 2 pcs, with quick mounting connection for installation on masts with a diameter of 51 ... 127 mm



Your advantages

- For mounting the Smart Ethernet Box
- made from high-quality stainless steel
- For outdoor installation
- Easy operation
- Rugged design

Commercial data

Item number	1175556
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN08
Product key	DNC3Z1
GTIN	4063151205799
Weight per piece (including packing)	146.3 g
Weight per piece (excluding packing)	140 g
Customs tariff number	73269098
Country of origin	DE

SCX-CLAMP 14X51-127 - Mast clamp



1175556

<https://www.phoenixcontact.com/us/products/1175556>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Mounting material
Manufacturer	Ideal Tridon
Manufacturer Designation	Surelock 48
Manufacturer product number	48001 0072

Connection data

Tightening torque	5.9 Nm (Recommended maximum torque for standard applications)
-------------------	---

Dimensions

Width	14.3 mm
-------	---------

Material specifications

Material (Strap and clamping part)	Stainless steel 1.4301/AISI 304
Material (Screw)	Stainless steel 1.4303/AISI 305

SCX-CLAMP 14X51-127 - Mast clamp



1175556

<https://www.phoenixcontact.com/us/products/1175556>

Classifications

ECLASS

ECLASS-13.0	23159090
ECLASS-15.0	23159090

ETIM

ETIM 10.0	EC011571
-----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

SCX-CLAMP 14X51-127 - Mast clamp



1175556

<https://www.phoenixcontact.com/us/products/1175556>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.033 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com