

SAC-6P- 1,5-PUR/M 8FS BK - Sensor/actuator cable



1182125

<https://www.phoenixcontact.com/us/products/1182125>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 6-position, free cable end, on Socket straight M8, cable length: 1.5 m

Commercial data

Item number	1182125
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1BGA
GTIN	4063151220020
Weight per piece (including packing)	56.6 g
Weight per piece (excluding packing)	56 g
Customs tariff number	85444290
Country of origin	PL

SAC-6P- 1,5-PUR/M 8FS BK - Sensor/actuator cable



1182125

<https://www.phoenixcontact.com/us/products/1182125>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	6

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Outer sheath, material	PUR
------------------------	-----

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A

Connection data

Conductor connection

Tightening torque	0.2 Nm
-------------------	--------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M8
Number of positions	6

Cable/line

Cable length	1.5 m
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-6P- 1,5-PUR/M 8FS BK - Sensor/actuator cable



1182125

<https://www.phoenixcontact.com/us/products/1182125>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-6P- 1,5-PUR/M 8FS BK - Sensor/actuator cable



1182125

<https://www.phoenixcontact.com/us/products/1182125>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com