

# UNIFOX SR 6 - Mounting pliers



1200137

<https://www.phoenixcontact.com/us/products/1200137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mounting pliers for snapping the SUNCLIX crimp contacts into the plastic housing, curved 35°, suitable for a conductor diameter of 4.2 mm ... 6.0 mm.

## Your advantages

- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- For mounting contacts without damage

## Commercial data

Item number	1200137
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH316S
GTIN	4055626162911
Weight per piece (including packing)	200.4 g
Weight per piece (excluding packing)	200 g
Customs tariff number	82032000
Country of origin	DE

# UNIFOX SR 6 - Mounting pliers



1200137

<https://www.phoenixcontact.com/us/products/1200137>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Assembly tool
Application	Aluminum
	Copper
	SUNCLIX contacts
Product property	Bent 35°
	Cutting edge is inductively hardened
	For mounting SUNCLIX contacts
	Ergonomic two-component handle

### Dimensions

Width	58 mm
Height	28 mm
Length	165 mm

#### External dimensions

Outside diameter	4.2 mm ... 6 mm
------------------	-----------------

### Material specifications

Color	black
-------	-------

### Cable/line

External cable diameter	≤ 6.00 mm
-------------------------	-----------

# UNIFOX SR 6 - Mounting pliers



1200137

<https://www.phoenixcontact.com/us/products/1200137>

## Classifications

### ECLASS

ECLASS-13.0	21043817
ECLASS-15.0	21043817

### ETIM

ETIM 10.0	EC000833
-----------	----------

### UNSPSC

UNSPSC 21.0	27112100
-------------	----------

# UNIFOX SR 6 - Mounting pliers

1200137

<https://www.phoenixcontact.com/us/products/1200137>



## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)