

CRIMPSET 6 - Tool set



1202072

<https://www.phoenixcontact.com/us/products/1202072>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assortment box, metal, assembled with ferrules in accordance with DIN 46228-4: 1990-09, 500 of each. AI 0,25-6 YE, AI 0,34-6 TQ, AI 0,5-8 WH, AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK, 300 pcs. AI 2,5-8 BU, 200 pcs. AI 4-10 GY, 100 pcs. AI 6-12 YE, CRIMPFOX DUO 10, QUICK WIREFOX 6

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Commercial data

Item number	1202072
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4017918017699
Weight per piece (including packing)	2,828 g
Weight per piece (excluding packing)	2,606.8 g
Customs tariff number	82060000
Country of origin	SE

CRIMPSET 6 - Tool set



1202072

<https://www.phoenixcontact.com/us/products/1202072>

Set consists of

AI 0,25- 6 YE - Ferrule

3203024

<https://www.phoenixcontact.com/us/products/3203024>



Ferrule, Length contact range: 6 mm, sleeve length: 10.5 mm, color: yellow

AI 0,34- 6 TQ - Ferrule

3203053

<https://www.phoenixcontact.com/us/products/3203053>



Ferrule, Length contact range: 6 mm, sleeve length: 10.5 mm, color: turquoise

CRIMPSET 6 - Tool set

1202072

<https://www.phoenixcontact.com/us/products/1202072>

AI 0,5 - 8 WH - Ferrule

3200014

<https://www.phoenixcontact.com/us/products/3200014>



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: white

AI 0,75- 8 GY - Ferrule

3200519

<https://www.phoenixcontact.com/us/products/3200519>



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: gray

CRIMPSET 6 - Tool set

1202072

<https://www.phoenixcontact.com/us/products/1202072>

AI 1 - 8 RD - Ferrule

3200030

<https://www.phoenixcontact.com/us/products/3200030>



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: red

AI 1,5 - 8 BK - Ferrule

3200043

<https://www.phoenixcontact.com/us/products/3200043>



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: black

CRIMPSET 6 - Tool set

1202072

<https://www.phoenixcontact.com/us/products/1202072>

AI 2,5 - 8 BU - Ferrule

3200522

<https://www.phoenixcontact.com/us/products/3200522>



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: blue

AI 4 -10 GY - Ferrule

3200535

<https://www.phoenixcontact.com/us/products/3200535>



Ferrule, Length contact range: 10 mm, sleeve length: 17 mm, color: gray

CRIMPSET 6 - Tool set

1202072

<https://www.phoenixcontact.com/us/products/1202072>



AI 6 -12 YE - Ferrule

3200548

<https://www.phoenixcontact.com/us/products/3200548>



Ferrule, Length contact range: 12 mm, sleeve length: 20 mm, color: yellow

QUICK WIREFOX 6 - Stripping pliers

1204384

<https://www.phoenixcontact.com/us/products/1204384>



Stripping pliers for cables with PVC insulation, stripping range: 0.08 to 6 mm², wire cutting up to 6 mm² flexible or 4 mm² rigid

CRIMPSET 6 - Tool set

1202072

<https://www.phoenixcontact.com/us/products/1202072>



CRIMPFOX DUO 10 - Crimping pliers

1031721

<https://www.phoenixcontact.com/us/products/1031721>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm², max. cross section: 10 mm², for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

CRIMPSET 6 - Tool set



1202072

<https://www.phoenixcontact.com/us/products/1202072>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Tool set

Compression

Trapezoidal crimp

Dimensions

Width

357 mm

Height

48 mm

Length

206 mm

Material specifications

Color

silver-colored

Base element material

Metal

CRIMPSET 6 - Tool set



1202072

<https://www.phoenixcontact.com/us/products/1202072>

Classifications

ECLASS

ECLASS-15.0	27400218
ECLASS-13.0	27400218

ETIM

ETIM 10.0	EC000524
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CRIMPSET 6 - Tool set



1202072

<https://www.phoenixcontact.com/us/products/1202072>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	42.73 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com