CRIMPSET 6 - Tool set

1202072

https://www.phoenixcontact.com/us/products/1202072

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assortment box, metal, assembled with ferrules in accordance with DIN 46228-4: 1990-09, 500 of each. AI 0,25-6 YE, AI 0,34-6 TQ, AI 0,5-8 WH, AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK, 300 pcs. AI 2,5-8 BU, 200 pcs. AI 4-10 GY, 100 pcs. AI 6-12 YE, CRIMPFOX DUO 10, QUICK WIREFOX 6

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Commercial data

Item number	1202072
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4017918017699
Weight per piece (including packing)	2,828 g
Weight per piece (excluding packing)	2,606.8 g
Customs tariff number	82060000
Country of origin	DE

Set consists of

AI 0,25- 6 YE - Ferrule

3203024

https://www.phoenixcontact.com/us/products/3203024



Ferrule, Length contact range: 6 mm, sleeve length: 10.5 mm, color: yellow

AI 0,34- 6 TQ - Ferrule

3203053

https://www.phoenixcontact.com/us/products/3203053



Ferrule, Length contact range: 6 mm, sleeve length: 10.5 mm, color: turquoise

AI 0,5 - 8 WH - Ferrule

3200014

https://www.phoenixcontact.com/us/products/3200014



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: white

AI 0,75- 8 GY - Ferrule

3200519

https://www.phoenixcontact.com/us/products/3200519



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: gray

AI 1 - 8 RD - Ferrule

3200030

https://www.phoenixcontact.com/us/products/3200030



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: red

AI 1,5 - 8 BK - Ferrule

3200043

https://www.phoenixcontact.com/us/products/3200043



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: black

AI 2,5 - 8 BU - Ferrule

3200522

https://www.phoenixcontact.com/us/products/3200522



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: blue

AI 4 -10 GY - Ferrule

3200535

https://www.phoenixcontact.com/us/products/3200535



Ferrule, Length contact range: 10 mm, sleeve length: 17 mm, color: gray

AI 6 -12 YE - Ferrule

3200548

https://www.phoenixcontact.com/us/products/3200548



Ferrule, Length contact range: 12 mm, sleeve length: 20 mm, color: yellow

QUICK WIREFOX 6 - Stripping pliers

1204384

https://www.phoenixcontact.com/us/products/1204384



Stripping pliers for cables with PVC insulation, stripping range: 0.08 to 6 mm^2, wire cutting up to 6 mm^2 flexible or 4 mm^2 rigid

CRIMPFOX DUO 10 - Crimping pliers

1031721

https://www.phoenixcontact.com/us/products/1031721



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm^2, max. cross section: 10 mm^2, for TWIN ferrules up to 2 x 4 mm^2, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Compression	Trapezoidal crimp

Dimensions

Width	357 mm
Height	48 mm
Length	206 mm

Material specifications

Color	silver-colored
Base element material	Metal

Classifications

ECLASS

ECLASS-15.0	27400218
ECLASS-13.0	27400218

ETIM

ETIM 10.0	EC000524

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	42.73 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com