

PPS STANDARD M - Cutting tool



1206175

<https://www.phoenixcontact.com/us/products/1206175>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile cutter, for cutting and stamping holes in standard DIN rails, NS 32/NS 35/7,5/NS 35 /15 and for cutting the NS 15 and NLS-CU 3/10 neutral busbar to length, can accommodate 2 stamping bits, with metric measuring rail, delivered without stamping bits

Your advantages

- Burr-free and chip-free cutting to length
- Cutting with minimal effort and less strain on joints thanks to optimum leverage
- Quick and convenient setting of the cutting length by means of a stop
- Precise and uniform cuts

Commercial data

Item number	1206175
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3115
GTIN	4017918163280
Weight per piece (including packing)	18,925 g
Weight per piece (excluding packing)	18,006 g
Customs tariff number	82034000
Country of origin	DE

PPS STANDARD M - Cutting tool



1206175

<https://www.phoenixcontact.com/us/products/1206175>

Technical data

Product properties

Product type	Profile cutters
Application	DIN rail and 2 hole punches for NS 15 / NS 32 / NS 35/7,5 / NS 35/15, and NLS-CU 3/10
Product property	Imperial/metric measuring rail 1 m with end stop
	Can be equipped with 2 punching machines (optional)
	Very robust design
	Burr-free and chip-free cutting
	Optimized leverage
	For table mounting (screw holes present)
	Compatible with PPS HYDRAULIC CYL 1208924

Dimensions

Width	180 mm
Height	220 mm
Length	100 mm
Length of the measuring bar	1000 mm
Length of the hand lever	860 mm
Max. material thickness	1.5 mm

Material specifications

Color	multicolored (RAL -)
Material	Steel

PPS STANDARD M - Cutting tool



1206175

<https://www.phoenixcontact.com/us/products/1206175>

Classifications

ECLASS

ECLASS-15.0	21043714
ECLASS-13.0	21043714

ETIM

ETIM 10.0	EC002212
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

PPS STANDARD M - Cutting tool



1206175

<https://www.phoenixcontact.com/us/products/1206175>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com