

CRIMPFOX RC 0,56 - Crimping pliers



1205529

<https://www.phoenixcontact.com/us/products/1205529>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for connector contacts 0.08 mm² - 0.56 mm²

Commercial data

Item number	1205529
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4017918129132
Weight per piece (including packing)	309.5 g
Weight per piece (excluding packing)	292 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX RC 0,56 - Crimping pliers



1205529

<https://www.phoenixcontact.com/us/products/1205529>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

Square crimp

Crimping position 1

Min. cross section

0.08 mm²

Max. cross section

0.2 mm²

AWG min

28

AWG max

24

Crimping position 2

Min. cross section

0.2 mm²

Max. cross section

0.56 mm²

AWG min

24

AWG max

20

Connection data

Conductor connection

Cross section range, metric

0.08 mm² ... 0.56 mm²

Dimensions

Width

55 mm

Length

195 mm

Material specifications

Color

black

CRIMPFOX RC 0,56 - Crimping pliers



1205529

<https://www.phoenixcontact.com/us/products/1205529>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1205529>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX RC 0,56 - Crimping pliers



1205529

<https://www.phoenixcontact.com/us/products/1205529>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX RC 0,56 - Crimping pliers



1205529

<https://www.phoenixcontact.com/us/products/1205529>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com