

# PPS CLASSIC I/M - Cutting tool



1206256

<https://www.phoenixcontact.com/us/products/1206256>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Profile cutter**, for cutting to length and stamping holes in standard DIN rails, NS 32/NS 35/7,5/NS 35/15, and for cutting to length the NS 15 and NLS-CU 3/10 neutral busbar, can accommodate 2 stamping bits, bits easily exchangeable, delivered without stamping bits, with inch/millimeter measuring rail

## Your advantages

- Burr-free and chip-free cutting to length
- Cutting with minimal effort and less strain on joints thanks to optimum leverage
- Quick and convenient setting of the cutting length by means of a stop
- Precise and uniform cuts

## Commercial data

Item number	1206256
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3115
GTIN	4017918166557
Weight per piece (including packing)	21,000 g
Weight per piece (excluding packing)	20,814 g
Customs tariff number	82034000
Country of origin	DE

# PPS CLASSIC I/M - Cutting tool



1206256

<https://www.phoenixcontact.com/us/products/1206256>

## Technical data

### Product properties

Product type	Profile cutters
Application	DIN rail and 2 hole punches for NS 15 / NS 32 / NS 35/7,5 / NS 35/15, and NLS-CU 3/10
Product property	Imperial/metric measuring rail 1 m with end stop
	Can be equipped with 2 punching machines (optional)
	Very robust design
	Burr-free and chip-free cutting
	Optimized leverage
	For table mounting (screw holes present)

### Dimensions

Width	250 mm
Height	230 mm
Length	100 mm
Length of the measuring bar	1000 mm
Length of the hand lever	860 mm
Max. material thickness	1.5 mm

### Material specifications

Color	multicolored (RAL -)
Material	Steel

# PPS CLASSIC I/M - Cutting tool



1206256

<https://www.phoenixcontact.com/us/products/1206256>

## Classifications

### ECLASS

ECLASS-13.0	21043714
ECLASS-15.0	21043714

### ETIM

ETIM 10.0	EC002212
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# PPS CLASSIC I/M - Cutting tool



1206256

<https://www.phoenixcontact.com/us/products/1206256>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)