

CRIMPFOX LC - Crimping pliers



1206696

<https://www.phoenixcontact.com/us/products/1206696>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Basic crimping pliers, with short handles, without crimp inserts, with locator takeup



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1206696 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH313A |
| GTIN | 4017918178840 |
| Weight per piece (including packing) | 654.5 g |
| Weight per piece (excluding packing) | 654.5 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

CRIMPFOX LC - Crimping pliers



1206696

<https://www.phoenixcontact.com/us/products/1206696>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

universal

Connection data

Conductor connection

Cross section range, metric

1 mm² ... 10 mm²

Dimensions

Width

80 mm

Length

220 mm

Material specifications

Color

black

CRIMPFOX LC - Crimping pliers

1206696

<https://www.phoenixcontact.com/us/products/1206696>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1206696>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX LC - Crimping pliers

1206696

<https://www.phoenixcontact.com/us/products/1206696>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX LC - Crimping pliers



1206696

<https://www.phoenixcontact.com/us/products/1206696>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com