

# PPS BASIC I/M - Cutting tool



1207585

<https://www.phoenixcontact.com/us/products/1207585>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Profile cutter**, for cutting standard DIN rails to length, NS 15 / NS 35/7,5 / NS 35/15, and for cutting the NLS-CU 3/10 neutral busbar to length, with inch/metric measuring rail

## Your advantages

- Burr-free and chip-free cutting to length
- Cutting with minimal effort and less strain on joints thanks to optimum leverage
- Quick and convenient setting of the cutting length by means of a stop
- Precise and uniform cuts

## Commercial data

Item number	1207585
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3115
GTIN	4017918895228
Weight per piece (including packing)	9,500 g
Weight per piece (excluding packing)	9,393 g
Customs tariff number	82034000
Country of origin	DE

# PPS BASIC I/M - Cutting tool



1207585

<https://www.phoenixcontact.com/us/products/1207585>

## Technical data

### Product properties

Product type	Profile cutters
Application	DIN rail for NS 15 /NS 35/7,5 / NS 35/15, and NLS-CU 3/10
Product property	Imperial/metric measuring rail 1 m with end stop
	Robust design
	Burr-free and chip-free cutting
	For table mounting (screw holes present)

### Dimensions

Width	150 mm
Height	180 mm
Length	60 mm
Length of the measuring bar	1000 mm
Length of the hand lever	610 mm
Max. material thickness	1.5 mm

### Material specifications

Color	multicolored (RAL -)
Material	Steel

# PPS BASIC I/M - Cutting tool



1207585

<https://www.phoenixcontact.com/us/products/1207585>

## Classifications

### ECLASS

ECLASS-15.0	21043714
ECLASS-13.0	21043714

### ETIM

ETIM 10.0	EC002212
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# PPS BASIC I/M - Cutting tool



1207585

<https://www.phoenixcontact.com/us/products/1207585>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)