

# CF 1000-TOOLKIT 0,34/6-8 - Conversion kit



1208226

<https://www.phoenixcontact.com/us/products/1208226>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation kit for CF 1000-1,5 from serial number 160594, for insulated ferrules in accordance with DIN 46228-4: 2017-05, cross section range: 0.25 ... 0.34 mm<sup>2</sup>, stripping length: 6 ... 8 mm

## Commercial data

Item number	1208226
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4055626041780
Weight per piece (including packing)	1,886 g
Weight per piece (excluding packing)	1,826 g
Customs tariff number	84799070
Country of origin	DE

# CF 1000-TOOLKIT 0,34/6-8 - Conversion kit



1208226

<https://www.phoenixcontact.com/us/products/1208226>

## Technical data

### Product properties

Product type	Conversion kit
Compression	Trapezoidal crimp

### Connection data

Conductor cross-section flexible	0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup>
----------------------------------	---

# CF 1000-TOOLKIT 0,34/6-8 - Conversion kit



1208226

<https://www.phoenixcontact.com/us/products/1208226>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1208226>



**EAC**

Approval ID: RU C-DE.AI30.B.01549

# CF 1000-TOOLKIT 0,34/6-8 - Conversion kit



1208226

<https://www.phoenixcontact.com/us/products/1208226>

## Classifications

### ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

### ETIM

ETIM 10.0	EC002778
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CF 1000-TOOLKIT 0,34/6-8 - Conversion kit



1208226

<https://www.phoenixcontact.com/us/products/1208226>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)