

CRIMPFOX-SC 6L - Crimping pliers



1212052

<https://www.phoenixcontact.com/us/products/1212052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for 2.8 / 4.8 / 6.3 mm non-insulated slip-on sleeves, three marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Your advantages

- Unlockable pressure lock
- Marked die stations for precise processing of corresponding cross sections
- Consistently high crimping quality

Commercial data

Item number	1212052
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3134
GTIN	4046356453943
Weight per piece (including packing)	1,026.1 g
Weight per piece (excluding packing)	1,026.1 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-SC 6L - Crimping pliers



1212052

<https://www.phoenixcontact.com/us/products/1212052>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	B crimp
Product property	Unlockable pressure lock
	Marked die stations

Crimping position 1

Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	22
AWG max	16

Crimping position 2

Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14

Crimping position 3

Min. cross section	2.5 mm ²
Max. cross section	6 mm ²
AWG min	14
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.5 mm ² ... 6 mm ²
Cross section range AWG	22 ... 10

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-SC 6L - Crimping pliers



1212052

<https://www.phoenixcontact.com/us/products/1212052>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212052>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-SC 6L - Crimping pliers



1212052

<https://www.phoenixcontact.com/us/products/1212052>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-SC 6L - Crimping pliers



1212052

<https://www.phoenixcontact.com/us/products/1212052>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com