

# CRIMPFOX 6S-F - Crimping pliers



1212043

<https://www.phoenixcontact.com/us/products/1212043>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, front entry, square crimp

## Your advantages

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Unlockable pressure lock
- Comprehensive range of crimping pliers
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections

## Commercial data

Item number	1212043
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356453875
Weight per piece (including packing)	460.69 g
Weight per piece (excluding packing)	426.16 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX 6S-F - Crimping pliers



1212043

<https://www.phoenixcontact.com/us/products/1212043>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

Square crimp

#### Crimping position 1

Min. cross section

0.5 mm<sup>2</sup>

Max. cross section

6 mm<sup>2</sup>

AWG min

20

AWG max

10

### Connection data

#### Conductor connection

Cross section range, metric

0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>

Cross section range AWG

20 ... 10

### Dimensions

Width

18 mm

Height

59 mm

Length

198 mm

### Material specifications

Color

black

# CRIMPFOX 6S-F - Crimping pliers


1212043

<https://www.phoenixcontact.com/us/products/1212043>



## Drawings

Product drawing



# CRIMPFOX 6S-F - Crimping pliers



1212043

<https://www.phoenixcontact.com/us/products/1212043>

## Classifications

### ECLASS

ECLASS-13.0

21043811

### ETIM

ETIM 9.0

EC000168

### UNSPSC

UNSPSC 21.0

27111500

# CRIMPFOX 6S-F - Crimping pliers



1212043

<https://www.phoenixcontact.com/us/products/1212043>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)