

# CRIMPFOX-CX 6,48 - Crimping pliers



1212095

<https://www.phoenixcontact.com/us/products/1212095>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimping pliers, for coaxial connectors, 5.41 mm, 6.48 mm, 1.69 mm, HEX crimp



## Your advantages

- Lateral conductor entry
- Unlockable pressure lock

## Commercial data

Item number	1212095
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3138
GTIN	4046356453882
Weight per piece (including packing)	437.8 g
Weight per piece (excluding packing)	437.8 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-CX 6,48 - Crimping pliers



1212095

<https://www.phoenixcontact.com/us/products/1212095>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

HEX crimp

Product property

Lateral conductor entry

Unlockable pressure lock

#### Crimping position 1

Crimping width

5.41 mm

#### Crimping position 2

Crimping width

6.48 mm

#### Crimping position 3

Crimping width

1.69 mm

### Connection data

#### Conductor connection

Cross section range, metric

1.69 mm<sup>2</sup> ... 6.48 mm<sup>2</sup>

### Dimensions

Width

18 mm

Height

59 mm

Length

198 mm

#### External dimensions

Outside diameter

1.69 mm ... 6.48 mm

### Material specifications

Color

black

# CRIMPFOX-CX 6,48 - Crimping pliers


1212095

<https://www.phoenixcontact.com/us/products/1212095>



## Drawings

Product drawing



# CRIMPFOX-CX 6,48 - Crimping pliers



1212095

<https://www.phoenixcontact.com/us/products/1212095>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212095>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-CX 6,48 - Crimping pliers



1212095

<https://www.phoenixcontact.com/us/products/1212095>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-CX 6,48 - Crimping pliers



1212095

<https://www.phoenixcontact.com/us/products/1212095>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)