

CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable cutter, precision blade with macro-notching, for copper and aluminum up to 70 mm², VDE 1000 V AC/ 1500 V DC tested

Your advantages

- VDE tested
- Special tool steel for permanent use
- Precision cutting edge with macro-notching
- Adjustable screw joint
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

Commercial data

Item number	1212127
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3113
GTIN	4046356454261
Weight per piece (including packing)	322 g
Weight per piece (excluding packing)	319.2 g
Customs tariff number	82032000
Country of origin	DE

CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Cutting tool
Application	Aluminum
	Copper
Product property	Toothed cutting surface with pre-cutting zone
	Optimized leverage
	Crush-free cutting
	Ergonomic two-component handle
	Adjustable screw joint
	VDE tested

Dimensions

Length	210 mm
Diameter	25 mm

External dimensions

Outside diameter	≤ 25 mm
------------------	---------

Material specifications

Color	multicolored (RAL -)
-------	----------------------

Cable/line

External cable diameter	≤ 25.00 mm
-------------------------	------------

Standards and regulations

Tests	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212127>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Classifications

ECLASS

ECLASS-13.0	21044701
ECLASS-15.0	21044701

ETIM

ETIM 10.0	EC000142
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	4.885 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com