

CRIMPFOX-RCT 25-1 - Crimping pliers



1212066

<https://www.phoenixcontact.com/us/products/1212066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated CU tubular cable lugs (DIN 46235), 10 mm² ... 25 mm², HEX crimp

Your advantages

- CRIMPFOX-RC 10 and ...RCT 25-1 complete the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this design reduce the amount of force required for crimping by 25%

Commercial data

Item number	1212066
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356454063
Weight per piece (including packing)	661.6 g
Weight per piece (excluding packing)	661.6 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-RCT 25-1 - Crimping pliers



1212066

<https://www.phoenixcontact.com/us/products/1212066>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	HEX crimp
Product property	Crimping of standardized connectors in accordance with DIN 46235 Up to 25% lower actuation force

Crimping position 1

Max. cross section	10 mm ²
AWG max	8
Outside diameter	7.00 mm
Internal diameter	4.50 mm

Crimping position 2

Max. cross section	16 mm ²
AWG max	6
Outside diameter	8.50 mm
Internal diameter	5.50 mm

Crimping position 3

Max. cross section	25 mm ²
AWG max	4
Outside diameter	10.00 mm
Internal diameter	7.00 mm

Connection data

Conductor connection

Cross section range, metric	10 mm ² ... 25 mm ²
Cross section range AWG	7 ... 2/0

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-RCT 25-1 - Crimping pliers



1212066

<https://www.phoenixcontact.com/us/products/1212066>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212066>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RCT 25-1 - Crimping pliers



1212066

<https://www.phoenixcontact.com/us/products/1212066>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-RCT 25-1 - Crimping pliers



1212066

<https://www.phoenixcontact.com/us/products/1212066>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com