

CUTFOX 12 - Cable-cutting tool



1212128

<https://www.phoenixcontact.com/us/products/1212128>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable cutter, for copper and aluminum up to 12 mm diameter (up to 35 mm²)

Your advantages

- Cutting various cable types and sizes
- Burr-free cutting without crushing
- Special tool steel for permanent use
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

Commercial data

Item number	1212128
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3112
GTIN	4046356456081
Weight per piece (including packing)	202.7 g
Weight per piece (excluding packing)	198 g
Customs tariff number	82032000
Country of origin	DE

CUTFOX 12 - Cable-cutting tool



1212128

<https://www.phoenixcontact.com/us/products/1212128>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Cutting tool
Application	Aluminum
	Copper
Product property	Two cutting and stripping areas
	Crush-free cutting
	Ergonomic two-component handle
	Riveted joint

Connection data

Conductor cross-section flexible	35 mm ²
----------------------------------	--------------------

Dimensions

Width	53 mm
Length	165 mm
Diameter	12 mm

Material specifications

Color	multicolored (RAL -)
-------	----------------------

Cable/line

External cable diameter	≤ 12.00 mm
-------------------------	------------

CUTFOX 12 - Cable-cutting tool



1212128

<https://www.phoenixcontact.com/us/products/1212128>

Classifications

ECLASS

ECLASS-13.0	21044701
ECLASS-15.0	21044701

ETIM

ETIM 10.0	EC000142
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CUTFOX 12 - Cable-cutting tool



1212128

<https://www.phoenixcontact.com/us/products/1212128>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com