

# CRIMPFOX-CX 9,14 - Crimping pliers



1212096

<https://www.phoenixcontact.com/us/products/1212096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimping pliers, for coaxial connectors, 8.23 mm, 9.14 mm, 1.73 mm, HEX crimp



## Your advantages

- Lateral conductor entry
- Unlockable pressure lock

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212096       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3138        |
| GTIN                                 | 4046356453998 |
| Weight per piece (including packing) | 674.7 g       |
| Weight per piece (excluding packing) | 673.6 g       |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# CRIMPFOX-CX 9,14 - Crimping pliers



1212096

<https://www.phoenixcontact.com/us/products/1212096>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

HEX crimp

Product property

Lateral conductor entry

Unlockable pressure lock

#### Crimping position 1

Crimping width

8.23 mm

#### Crimping position 2

Crimping width

9.14 mm

#### Crimping position 3

Crimping width

1.73 mm

### Connection data

#### Conductor connection

Cross section range, metric

1.73 mm<sup>2</sup> ... 9.14 mm<sup>2</sup>

### Dimensions

Width

25 mm

Height

68 mm

Length

256 mm

#### External dimensions

Outside diameter

1.73 mm ... 9.14 mm

### Material specifications

Color

black

# CRIMPFOX-CX 9,14 - Crimping pliers



1212096

<https://www.phoenixcontact.com/us/products/1212096>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212096>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-CX 9,14 - Crimping pliers



1212096

<https://www.phoenixcontact.com/us/products/1212096>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-CX 9,14 - Crimping pliers



1212096

<https://www.phoenixcontact.com/us/products/1212096>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)