

CUTFOX-FBS - Front cutter



1212124

<https://www.phoenixcontact.com/us/products/1212124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting tool, for separating individual jumper bars from FBS ... plug-in bridges and EB ... insertion bridges

Your advantages

- Inductively hardened blades for long-term stable cutting performance
- VDE tested
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Precision cutting edge for the corresponding application

Commercial data

Item number	1212124
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH311S
GTIN	4046356454247
Weight per piece (including packing)	222.6 g
Weight per piece (excluding packing)	296 g
Customs tariff number	82032000
Country of origin	DE

CUTFOX-FBS - Front cutter



1212124

<https://www.phoenixcontact.com/us/products/1212124>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Cutting tool
Application	Plug-in bridges
Product property	Front cutter for notching FBS and EB bridges
	Inductively hardened precision cutting edge
	Ergonomic two-component handle
	Minimum force required
	Special tool steel, die-forged and oil-hardened\

Dimensions

Width	60 mm
Height	30 mm
Length	190 mm

Material specifications

Color	multicolored (RAL -)
Material	Steel with plastic handle

Cable/line

External cable diameter	0.2 mm ... 3.5 mm
-------------------------	-------------------

CUTFOX-FBS - Front cutter



1212124

<https://www.phoenixcontact.com/us/products/1212124>

Classifications

ECLASS

ECLASS-13.0	21043712
ECLASS-15.0	21043712

ETIM

ETIM 10.0	EC002222
-----------	----------

UNSPSC

UNSPSC 21.0	22101700
-------------	----------

CUTFOX-FBS - Front cutter



1212124

<https://www.phoenixcontact.com/us/products/1212124>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com