

# WIREFOX 4 - Stripping tool



1212156

<https://www.phoenixcontact.com/us/products/1212156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for cables and conductors (especially for rubber and silicone insulations) from 0.1 - 4 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

## Product description

Insertable stripping blades: 1212152 WIREFOX 10/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212151 WIREFOX 4/SB

## Your advantages

- Flexible, adjustable limit stop for the stripping length
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters
- Practical integrated wire cutter

## Commercial data

Item number	1212156
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3121
GTIN	4046356454421
Weight per piece (including packing)	212.5 g
Weight per piece (excluding packing)	211.7 g
Customs tariff number	82032000
Country of origin	SE

# WIREFOX 4 - Stripping tool

1212156

<https://www.phoenixcontact.com/us/products/1212156>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Stripping tool
Application	Standard
	Silicone
	Rubber
Product property	Automatic adjustment mechanism
	Tool-free replacement of stripping blades
	Length stop for setting the stripping length $\leq 18$ mm
	Integrated wire cutter

### Connection data

#### Conductor connection

Cross section range, metric	0.1 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Stripping range)
	1.5 mm <sup>2</sup> (Cutting zone)
Cross section range AWG	28 ... 12 (Stripping range)
	16 (Cutting zone)
Stripping length	2 mm ... 18 mm

### Dimensions

Width	20 mm
Height	90 mm
Length	191 mm

### Material specifications

Color	black/green
-------	-------------

# WIREFOX 4 - Stripping tool

1212156

<https://www.phoenixcontact.com/us/products/1212156>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212156>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX 4 - Stripping tool

1212156

<https://www.phoenixcontact.com/us/products/1212156>



## Classifications

### ECLASS

ECLASS-13.0	21043706
ECLASS-15.0	21043706

### ETIM

ETIM 10.0	EC002109
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# WIREFOX 4 - Stripping tool



1212156

<https://www.phoenixcontact.com/us/products/1212156>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)