


# CF 500/COV RCI - Covering hood



1212255

<https://www.phoenixcontact.com/us/products/1212255>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hood for CF 500 automatic crimping device, for insulated cable lugs: 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup> (RCI 1.5, RCI 6, RCI 6-1), for turned contacts: 0.14 mm<sup>2</sup> ... 4 mm<sup>2</sup> (TC HC 4), for solar contacts: 0.25 mm<sup>2</sup> ... 6 mm<sup>2</sup> (SR 6-2)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212255       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH32          |
| Product key                          | BH323Z        |
| GTIN                                 | 4046356450171 |
| Weight per piece (including packing) | 42.2 g        |
| Weight per piece (excluding packing) | 42 g          |
| Customs tariff number                | 84799070      |
| Country of origin                    | DE            |

# CF 500/COV RCI - Covering hood



1212255

<https://www.phoenixcontact.com/us/products/1212255>

## Technical data

### Notes

|         |   |
|---------|---|
| General | Protective hood for CF 500 automatic crimping device, for insulated cable lugs 0.14 ... 6 mm <sup>2</sup> (RCI 1.5/6) and turned contacts 0.14 ... 4 mm <sup>2</sup> (TC 4) |
|---------|---|

### Product properties

|              |       |
|--------------|-------|
| Product type | Cover |
|--------------|-------|

### Connection data

|                                  |  |
|----------------------------------|--|
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
|----------------------------------|--|

### Dimensions

|        |         |
|--------|---------|
| Width  | 22.5 mm |
| Height | 70 mm   |
| Length | 105 mm  |

### Material specifications

|                               |             |
|-------------------------------|-------------|
| Color                         | transparent |
| Material                      | Plastic     |
| Material for screw connection | Metal       |

# CF 500/COV RCI - Covering hood



1212255

<https://www.phoenixcontact.com/us/products/1212255>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 17130192 |
| ECLASS-15.0 | 17130192 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002778 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CF 500/COV RCI - Covering hood



1212255

<https://www.phoenixcontact.com/us/products/1212255>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)