


# CF 500/DIE SC 1,5 - Crimp insert

1212241

<https://www.phoenixcontact.com/us/products/1212241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for slip-on sleeves and spade connectors (C-SCF... and C-SCM...) 0.1 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212241       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH32          |
| Product key                          | BH323Z        |
| GTIN                                 | 4046356449991 |
| Weight per piece (including packing) | 73.7 g        |
| Weight per piece (excluding packing) | 73.7 g        |
| Customs tariff number                | 84799070      |
| Country of origin                    | DE            |

# CF 500/DIE SC 1,5 - Crimp insert



1212241

<https://www.phoenixcontact.com/us/products/1212241>

## Technical data

### Product properties

|                    |                      |
|--------------------|----------------------|
| Product type       | Die                  |
| Compression        | B crimp              |
| Min. cross section | 0.14 mm <sup>2</sup> |
| Max. cross section | 1.5 mm <sup>2</sup>  |

### Connection data

#### Conductor connection

|                             |   |
|-----------------------------|---|
| Cross section range, metric | 0.1 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
|-----------------------------|---|

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Steel          |

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 0.5 mm ... 1.5 mm |
|-------------------------|-------------------|

# CF 500/DIE SC 1,5 - Crimp insert



1212241

<https://www.phoenixcontact.com/us/products/1212241>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212241>



**EAC**

Approval ID: RU C-DE.AI30.B.01549

# CF 500/DIE SC 1,5 - Crimp insert



1212241

<https://www.phoenixcontact.com/us/products/1212241>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 17130192 |
| ECLASS-15.0 | 17130192 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002778 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CF 500/DIE SC 1,5 - Crimp insert



1212241

<https://www.phoenixcontact.com/us/products/1212241>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 22.439 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)