

# SF-PHSL 1-80 VDE - Screwdriver



1212283

<https://www.phoenixcontact.com/us/products/1212283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screwdriver, positive/negative PH slot, VDE-isolated, size: PH 1 x 80, two component handle, with non-slip grip

## Your advantages

- Screwdrivers for Phillips screws with Pozidriv and Phillips Recess screw head
- VDE approval

## Commercial data

Item number	1212283
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3145
GTIN	4046356455183
Weight per piece (including packing)	61.37 g
Weight per piece (excluding packing)	61.37 g
Customs tariff number	82054000
Country of origin	CZ

# SF-PHSL 1-80 VDE - Screwdriver



1212283

<https://www.phoenixcontact.com/us/products/1212283>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration


### Product properties

Product type	Screwdriver tools
Type	Phillips
Product property	Kraftform handle
	Two-component handle
	Hexagonal non-slip grip
	Phillips Recess/slotted screw head

### Connection data

Output	Phillips Recess/plus-minus
--------	----------------------------

### Dimensions

Dimensional drawing	
Width	26 mm
Blade width	4.5 mm
Blade height	80 mm
Length	178 mm
Wrench size	0 mm
Wrench size for mounting	0 mm

### Material specifications

Material	alloyed tool steel
----------	--------------------

### Standards and regulations

Tests	IEC 60900:2004
-------	----------------

# SF-PHSL 1-80 VDE - Screwdriver


1212283

<https://www.phoenixcontact.com/us/products/1212283>



## Drawings

Dimensional drawing



# SF-PHSL 1-80 VDE - Screwdriver



1212283

<https://www.phoenixcontact.com/us/products/1212283>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212283>



**EAC**

Approval ID: RU C-DE.AI30.B.01750



**VDE Zeichengenehmigung**

Approval ID: 086858



**EAC**

Approval ID: 7500525.13.12.00701

# SF-PHSL 1-80 VDE - Screwdriver



1212283

<https://www.phoenixcontact.com/us/products/1212283>

## Classifications

### ECLASS

ECLASS-13.0	21040406
ECLASS-15.0	21040406

### ETIM

ETIM 10.0	EC000144
-----------	----------

### UNSPSC

UNSPSC 21.0	27111700
-------------	----------

# SF-PHSL 1-80 VDE - Screwdriver



1212283

<https://www.phoenixcontact.com/us/products/1212283>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.975 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)