

TSD 25 SAC - Torque screwdriver

1212315

<https://www.phoenixcontact.com/us/products/1212315>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Torque screwdriver, with preset torque of 2.5 Nm and 4 mm hexagonal drive for the pressure nut of the connector hood

The figure shows the TSD 04 SAC version

Your advantages

- TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm
- For the TSD-M... torque screwdrivers the torque can be set individually
- The TSD-M... adapters can accommodate the various nuts
- Wide range of SAC... nuts for various different applications

Commercial data

Item number	1212315
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH314A
GTIN	4046356455596
Weight per piece (including packing)	101.4 g
Weight per piece (excluding packing)	100 g
Customs tariff number	82054000
Country of origin	CZ

TSD 25 SAC - Torque screwdriver



1212315

<https://www.phoenixcontact.com/us/products/1212315>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Torque tool
Type	Hexagonal SW4

Connection data

Torque range	2.5 Nm ... 2.5 Nm
Output	External hexagonal

Dimensions

Width	37 mm
Blade width	0 mm
Blade height	100 mm
Length	205 mm
Blade thickness	0 mm

Material specifications

Color	black
-------	-------

TSD 25 SAC - Torque screwdriver



1212315

<https://www.phoenixcontact.com/us/products/1212315>

Classifications

ECLASS

ECLASS-13.0	21040417
ECLASS-15.0	21040417

ETIM

ETIM 10.0	EC002132
-----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

TSD 25 SAC - Torque screwdriver



1212315

<https://www.phoenixcontact.com/us/products/1212315>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	4.721 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com