

CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Basic pliers, for accommodating dies for a wide range of type of contacts up to 120 mm²



Your advantages

- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly
- Wide variety of available dies

Commercial data

Item number	1212318
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313A
GTIN	4046356454643
Weight per piece (including packing)	2,675 g
Weight per piece (excluding packing)	2,489.9 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

Product properties

Product type	Crimping tool
Compression	universal
Product property	Basic pliers for accommodating dies
	Joint head for bulky connector shapes
	With ratchet mechanism
	Two-hand operation
	Unlockable pressure lock
	Robust and long-lasting

Connection data

Conductor connection

Cross section range, metric	6 mm ² ... 120 mm ²
Cross section range AWG	10 ... 4/0

Dimensions

Width	130 mm
Height	65 mm
Length	430 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212318>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
-----------------------------------------	-------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	71.299 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com