

CRIMPFOX-C120 R35-70/DIE - Crimp insert

1212325

<https://www.phoenixcontact.com/us/products/1212325>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



pre-round die (pair), for CRIMPFOX-C120, for sector cable 35 + 70 mm²

Commercial data

Item number	1212325
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454711
Weight per piece (including packing)	161.4 g
Weight per piece (excluding packing)	161.4 g
Customs tariff number	82079091
Country of origin	DE

CRIMPFOX-C120 R35-70/DIE - Crimp insert



1212325

<https://www.phoenixcontact.com/us/products/1212325>

Technical data

Product properties

Product type	Die
Compression	Oval crimp
Product property	Replacement insert for CRIMPFOX-C120 crimping pliers
Min. cross section	35 mm ²
Max. cross section	70 mm ²

Connection data

Conductor connection

Cross section range, metric	35 mm ² ... 70 mm ²
-----------------------------	---

Material specifications

Color	black
-------	-------

CRIMPFOX-C120 R35-70/DIE - Crimp insert



1212325

<https://www.phoenixcontact.com/us/products/1212325>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212325>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-C120 R35-70/DIE - Crimp insert



1212325

<https://www.phoenixcontact.com/us/products/1212325>

Classifications

ECLASS

ECLASS-13.0	21043892
ECLASS-15.0	21043892

ETIM

ETIM 10.0	EC011822
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-C120 R35-70/DIE - Crimp insert



1212325

<https://www.phoenixcontact.com/us/products/1212325>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com