

# CRIMPFOX-C120 R95/DIE - Replacement die

1212326

<https://www.phoenixcontact.com/us/products/1212326>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pre-round die (pair), for CRIMPFOX-C120, for sector cable 95 mm<sup>2</sup>



## Commercial data

Item number	1212326
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454728
Weight per piece (including packing)	161.7 g
Weight per piece (excluding packing)	161.7 g
Customs tariff number	82079091
Country of origin	DE

# CRIMPFOX-C120 R95/DIE - Replacement die



1212326

<https://www.phoenixcontact.com/us/products/1212326>

## Technical data

### Product properties

Product type	Die
Compression	Oval crimp
Product property	Replacement insert for CRIMPFOX-C120 crimping pliers
Max. cross section	95 mm <sup>2</sup>
AWG max	3/0

### Connection data

#### Conductor connection

Cross section range, metric	= 95 mm <sup>2</sup> ... 95 mm <sup>2</sup>
-----------------------------	---

### Material specifications

Color	black
-------	-------

# CRIMPFOX-C120 R95/DIE - Replacement die



1212326

<https://www.phoenixcontact.com/us/products/1212326>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212326>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-C120 R95/DIE - Replacement die



1212326

<https://www.phoenixcontact.com/us/products/1212326>

## Classifications

### ECLASS

ECLASS-13.0	21043892
ECLASS-15.0	21043892

### ETIM

ETIM 10.0	EC011822
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-C120 R95/DIE - Replacement die



1212326

<https://www.phoenixcontact.com/us/products/1212326>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)