

# CRIMPFOX-C50 - Crimping pliers



1212340

<https://www.phoenixcontact.com/us/products/1212340>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Basic pliers, for accommodating dies for a wide range of type of contacts up to 50 mm<sup>2</sup>



## Your advantages

- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly
- Wide variety of available dies

## Commercial data

Item number	1212340
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313A
GTIN	4046356454865
Weight per piece (including packing)	1,619 g
Weight per piece (excluding packing)	1,527.2 g
Customs tariff number	82055980
Country of origin	DE

# CRIMPFOX-C50 - Crimping pliers



1212340

<https://www.phoenixcontact.com/us/products/1212340>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Crimping tool
Compression	universal
Product property	Basic pliers for accommodating dies
	Joint head for bulky connector shapes
	With ratchet mechanism
	Unlockable pressure lock
	Robust and long-lasting

### Connection data

#### Conductor connection

Cross section range, metric	6 mm <sup>2</sup> ... 70 mm <sup>2</sup>
Cross section range AWG	10 ... 2/0

### Dimensions

Width	60 mm
Height	65 mm
Length	280 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-C50 - Crimping pliers



1212340

<https://www.phoenixcontact.com/us/products/1212340>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212340>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-C50 - Crimping pliers



1212340

<https://www.phoenixcontact.com/us/products/1212340>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-C50 - Crimping pliers



1212340

<https://www.phoenixcontact.com/us/products/1212340>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	51.414 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)