

CRIMPFOX-C120 AI 70/M-DIE - Crimp insert



1212335

<https://www.phoenixcontact.com/us/products/1212335>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 70 mm², trapeze crimp



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212335 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH313Z |
| GTIN | 4046356454810 |
| Weight per piece (including packing) | 72.4 g |
| Weight per piece (excluding packing) | 73.5 g |
| Customs tariff number | 82079091 |
| Country of origin | DE |

CRIMPFOX-C120 AI 70/M-DIE - Crimp insert



1212335

<https://www.phoenixcontact.com/us/products/1212335>

Technical data

Product properties

| | |
|------------------|--|
| Product type | Die |
| Compression | universal |
| Product property | Replacement insert for CRIMPFOX-C120 crimping pliers |
| Crimping width | 26.00 mm |

Connection data

Conductor connection

| | |
|-----------------------------|---|
| Cross section range, metric | 50 mm ² ... 70 mm ² |
| Cross section range AWG | 1/0 ... 2/0 |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX-C120 AI 70/M-DIE - Crimp insert



1212335

<https://www.phoenixcontact.com/us/products/1212335>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212335>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-C120 AI 70/M-DIE - Crimp insert



1212335

<https://www.phoenixcontact.com/us/products/1212335>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043892 |
| ECLASS-15.0 | 21043892 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC011822 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-C120 AI 70/M-DIE - Crimp insert



1212335

<https://www.phoenixcontact.com/us/products/1212335>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 6.351 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com