

CRIMPFOX-C50 R50-70/DIE - Crimp insert



1212351

<https://www.phoenixcontact.com/us/products/1212351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

pre-round die (pair), for CRIMPFOX-C50, for sector cable 50 + 70 mm²



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212351 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH313Z |
| GTIN | 4046356455077 |
| Weight per piece (including packing) | 86.9 g |
| Weight per piece (excluding packing) | 80.82 g |
| Customs tariff number | 82079091 |
| Country of origin | DE |

CRIMPFOX-C50 R50-70/DIE - Crimp insert



1212351

<https://www.phoenixcontact.com/us/products/1212351>

Technical data

Product properties

| | |
|--------------------|---|
| Product type | Die |
| Compression | Oval crimp |
| Product property | Replacement insert for CRIMPFOX-C50 crimping pliers |
| Min. cross section | 50 mm ² |
| Max. cross section | 70 mm ² |
| AWG min | 2/0 |
| AWG max | 1/0 |

Connection data

Conductor connection

| | |
|-----------------------------|---|
| Cross section range, metric | 50 mm ² ... 70 mm ² |
|-----------------------------|---|

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX-C50 R50-70/DIE - Crimp insert



1212351

<https://www.phoenixcontact.com/us/products/1212351>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212351>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-C50 R50-70/DIE - Crimp insert



1212351

<https://www.phoenixcontact.com/us/products/1212351>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 21043892 |
| ECLASS-13.0 | 21043892 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC011822 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-C50 R50-70/DIE - Crimp insert



1212351

<https://www.phoenixcontact.com/us/products/1212351>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com