WIREFOX 2,5 - Stripping tool

1212368

https://www.phoenixcontact.com/us/products/1212368

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for conductors and cables with a conductor cross-section from 0.08 to 2.5 mm, self-adjusting, stripping length adjustable up to 15 mm, cutting capacity up to 6 mm^2 stranded/1.5 mm^2 solid

Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Commercial data

Item number	1212368
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3121
GTIN	4046356456128
Weight per piece (including packing)	180.5 g
Weight per piece (excluding packing)	174.8 g
Customs tariff number	82032000
Country of origin	GB

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Stripping tool
Application	Standard
Product property	Automatic adjustment mechanism
	Tool-free replacement of stripping blades
	Length stop for setting the stripping length ≤15 mm
	Angled pliers contour
	Integrated wire cutter
	Lamella knife also suitable for special insulation

Connection data

Conductor connection

Cross section range, metric	0.08 mm² ... 2.5 mm² (Stripping range)
	6 mm² (Cutting zone)
Cross section range AWG	28 ... 12 (Stripping range)
	10 (Cutting zone)
Stripping length	15 mm

Dimensions

Length	160 mm

Material specifications

Color	black (RAL 9005)

Cable/line

External cable diameter	0.3 mm ... 1.9 mm

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212368

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043706
ECLASS-15.0	21043706

ETIM

ETIM 10.0	EC002109

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	5.399 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com